

ALPHA

3477UFP200P63 TFR

EAN 4031582391039



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	240 mm
Overall weight	2.99 kg

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	46 mm
Hardness of tread (A)	65 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Swivel radius	167 mm
Swivel interference	334 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ALPHA

3477UFP200P63 TFR

EAN 4031582391039



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

