

SUPRATECH

PJP125X32-Ø8 55SH

EAN 4031582453935



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	8 mm
Hub length	36.5 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.276 kg

SUPRATECH

PJP125X32-Ø8 55SH

EAN 4031582453935



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

