

# LINEA LIGHT

A920PJI075L51-10 RAL7001

EAN 4031582377644



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●○○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda Linea light

Tip Okretanje Tocak

Standard EN12528 - tockovi za nameštaj

Nosivost na 3 km/h 60 kg

Statički Nosivost 120 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

Sveukupna visina 75,5 mm

Ukupna širina 55 mm

Ukupna težina 0,145 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	klizni lezaj sa caura cevi
štitnici omotaca	Bez stražara
Prečnik	75 mm
Širina omotac	15 mm
Teškoća gazećeg omotac (A)	92 Šor A

## KUCISTE

Materijal	polipropilen
oblik viljuska	kuciste za dva Tocak
okretni lezaj	stablo , okretanje
Boja	Srebrna siva (RAL7001)
ofset	23 mm
okretni radijus	65 mm
Otpor okretanju	130 mm
Prečnik kupole	30 mm

## PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

Deutscher  
dizajner  
ClubInterzum  
nagradaIF nagrada za  
Dizajn

# LINEA LIGHT

A920PJI075L51-10 RAL7001

EAN 4031582377644



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

