

AGILA

2477PIP125R05-22 TFR

EAN 4031582389272



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	163 mm
Overall weight	1.058 kg

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	131 mm
Swivel interference	262 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	22 mm
Bolt length	45 mm

AGILA

2477PIP125R05-22 TFR

EAN 4031582389272



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

