

# LEVINA

5377PJP125P30-13 XL 7001/3000

EAN 4031582382235



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Levina                        |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 104 °F                        |
| Overall height              | 6.34 in                       |
| Overall width               | 2.32 in                       |
| Overall weight              | 1.26 lb                       |

## HOUSING

|                     |                       |
|---------------------|-----------------------|
| Housing Material    | Polyamide             |
| Fork shape          | Slim                  |
| Swivel bearing      | Two ball races        |
| Housing Color       | Silver gray (RAL7001) |
| Offset              | 1.5 in                |
| Swivel radius       | 5.12 in               |
| Swivel interference | 10.24 in              |
| Dome diameter       | 2.32 in               |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver gray (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 4.92 in                |
| Tread width           | 1.26 in                |
| Body width            | 1.26 in                |
| Hardness of tread (A) | 87 Shore A             |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.51 in   |



Universal  
Design  
Award



Deutscher  
Designer  
Club

# LEVINA

5377PJP125P30-13 XL 7001/3000

EAN 4031582382235

Order number 00062306

Product Drawings



BETTER MOBILITY. BETTER LIFE.

