

# PURETECH

PIR 200x50-Ø20

EAN 4031582320381



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○   |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Puretech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 451.95 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 903.89 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 3.39 lb                       |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Roller bearing            |
| Wheel color           | Graphite black (RAL9011)  |
| Threadguards          | Without threadguard       |
| Diameter              | 7.87 in                   |
| Tread width           | 1.97 in                   |
| Axle hole diameter    | 0.79 in                   |
| Hub length            | 2.36 in                   |
| Body width            | 1.97 in                   |
| Hardness of tread (A) | 80 Shore A                |

# PURETECH

PIR 200x50-Ø20

EAN 4031582320381

Order number 00050619

Product Drawings



BETTER MOBILITY. BETTER LIFE.

