

SUPRATECH

PJP 100x35-Ø8,3 HL45 65A 9011/5015

EAN 4031582410549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Electric conductive	no
Stainless	no
Load capacity Static	551.16 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.53 lb

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Graphite black (RAL9011)
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.38 in
Hardness of tread (A)	65 Shore A

SUPRATECH

PJP 100x35-Ø8,3 HL45 65A 9011/5015

EAN 4031582410549

Order number 00063522
Product Drawings



BETTER MOBILITY. BETTER LIFE.

