

PURETECH

PVO250X50-Ø20,1 HL58 TRG

EAN 4031582404265



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, black |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 9.84 in |
| Tread width | 1.97 in |
| Axle hole diameter | 0.79 in |
| Hub length | 2.28 in |
| Hardness of tread (A) | 85 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ○ ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Puretech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 396.83 lb |
| Load capacity Static | 793.66 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 4.49 lb |

PURETECH

PVO250X50-Ø20,1 HL58 TRG

EAN 4031582404265



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

