

ICS

5327UAX125R05-18X62 INOX

EAN 4031582367546



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------|
| Roll performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●●● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | ICS |
| Housing type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 6.38 in |
| Overall weight | 1.71 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing, sealed |
| Threadguards | Integrated threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|-----------------|
| Material | Polyamide |
| Fork shape | Slim |
| Swivel bearing | Stem, swiveling |
| Offset | 1.5 in |
| Swivel interference | 10.2 in |
| Stainless | ✓ |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 0.71 in |
| Bolt length | 2.44 in |



IF
Design
Award

ICS


5327UAX125R05-18X62 INOX

EAN 4031582367546



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



IF
Design
Award