

NOVATECH

FTP 125X40-Ø20 HL50

EAN 4031582331745
Broj porudžbine 00841087

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	480 kg
Nosivost na 6 km/h	400 kg
Statički Nosivost	800 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,51 kg

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	20 mm
dužina glavcine	50 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6204ZV
Pogodno za	bt

NOVATECH

FTP 125X40-Ø20 HL50

EAN 4031582331745
Broj porudžbine 00841087



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

