

ULTRATECH

FCP200X50-Ø20-75SHA-SOFT

EAN 4031582479010



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Cast iron |
| Tread material | Ultratech Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Axle hole diameter | 20 mm |
| Hub length | 60 mm |
| Hardness of tread (A) | 75 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Ultratech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 1000 kg |
| Load capacity at 6 km/h | 800 kg |
| Load capacity Static | 2000 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 1.3 kg |