

PRODUCT INFORMATION

MONO

5025PJH080L51-10 RAL7035 REGULAR BRAKE

EAN 4031582460599



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor with wheel brake
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Overall height	4.09 in
Overall weight	0 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.94 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Color	Light gray (RAL7035)
Offset	1.34 in
Swivel interference	5.83 in

MONO

5025PJH080L51-10 RAL7035 REGULAR BRAKE

EAN 4031582460599



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

