

# ELASTECH HEAT

IDG100X35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Elastech heat
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Electric conductive	✓
Load capacity Static	352.74 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	482 °F
Overall weight	0.78 lb

## WHEEL

Body material	Aluminum
	soft
Tread material	Damping, heat resistant
Bearing	Dry bearing bush
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.31 in
Hub length	1.77 in
Hardness of tread (A)	75 Shore A

# ELASTECH HEAT

IDG100X35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

