

AGILA

267FPJP3X1.25P30-13

EAN 4031582435276



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance ● ● ● ○ ○

Movement noise ● ● ○ ○ ○

Attrition ● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Castor with butterfly wheel brake
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Overall height	100 mm

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	76.2 mm
Tread width	31.75 mm
Axle hole diameter	10 mm
Hardness of tread (A)	77 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	36 mm
Swivel radius	73.5 mm
Swivel interference	148.2 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm
Hint	Castors can be mounted with standard screws of any length.