

INTEGRAL

2040UAX200R05-32 9002 W

EAN 4031582300154
Order number 00030458



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Integral
Housing type	Swivel castor
Standard	EN12531 - Hospital Bed Castors
Load capacity at 3 km/h	150 kg
Load capacity at 4 km/h	150 kg
Load capacity Static	450 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	229 mm
Overall width	70 mm
Overall weight	1.616 kg
Certification	Tested and monitored by TÜV Süd

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing, sealed
Tread color	Slate grey (RAL7015)
Wheel color	Slate grey (RAL7015)
Threadguards	Integrated threadguard
Diameter	200 mm
Tread width	35 mm
Body width	35 mm
Hardness of tread (D)	59 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Closed
Swivel bearing	Precision ball bearing
Colour	Grey white (RAL9002)
Offset	60 mm
Swivel radius	160 mm
Swivel interference	320 mm
Dome diameter	70 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	32 mm
Bolt length	45 mm
Bolt thread position	7 mm
Bolt mounting holes quantity	2
Hint	Washable beds must be sealed in the fitting area by the hospital bed manufacturer.

ADDITIONAL INFORMATION

Washable according AK-BWA



IF
Design
Award



Red Dot
Design
Award

INTEGRAL

2040UAX200R05-32 9002 W

EAN 4031582300154
Order number 00030458



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

