

ELASTECH

IEP 250x50-Ø25 HL60

EAN 4031582319767



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Crni mlaz (sličan RAL9005)
stitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Nosivost na 6 km/h	400 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	2.34 kg

ELASTECH


IEP 250x50-Ø25 HL60

EAN 4031582319767

Broj porudžbine 00801257
Product Drawings



BETTER MOBILITY. BETTER LIFE.




ELASTECH

IEP 250x50-Ø25 H1.60

EAN 4031582319767

Broj porudžbine 00802257



BETTER MOBILITY. BETTER LIFE.