PRODUCT INFORMATION

AGILA STAINLESS

7475PJO050P40

EAN 4031582350975

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Agila stainless
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	69 mm
Overall width	43 mm
Overall weight	0.2 kg

HOUSING

Housing Material	Stainless steel, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Stainless steel
Offset	24 mm
Swivel radius	70 mm
Swivel interference	140 mm
Material brake pedal	polyamide
Dome diameter	41 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

© Copyright 2026 TENTE International GmbH


AGILA STAINLESS


7475PJO050P40


EAN 4031582350975

Order number 00036676

Product Drawings







© Copyright 2026 TENTE International GmbH