

ALPHA

3470DVR100R05-20X45

EAN 4031582303575



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ○ ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip kućišta	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	70 kg
Statički Nosivost	140 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	131 mm
Ukupna težina	1,046 kg

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	30 mm
Teškoća gazećeg omotac (A)	85 Šora A

KUCISTE

Materijal	Čelični list, težak
oblik viljusa	siroko
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	91 mm
Otpor okretanju	182 mm

PRILAGOĐAVANJE

Tip uklapanja	stablo, okrugla
Prečnik sraf	20 mm
Dužina sraf	45 mm

ALPHA

3470DVR100R05-20X45

EAN 4031582303575



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

