


# FOOTMASTER

FOOT MASTER GASD-075-ASF-HUD

EAN 4031582495201



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ○ ○ ○ ○ ○ |
| Buka u pokretu         | ○ ○ ○ ○ ○ |
| Ishrana                | ○ ○ ○ ○ ○ |
| otpornost na rdju      | ○ ○ ○ ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                 |
|--------------------------------|-----------------|
| Naziv proizvoda                | Footmaster      |
| Tip                            | Okretanje Tocak |
| Nosivost na 3 km/h             | 250 kg          |
| Električni provod              | no              |
| nerdjajuci                     | no              |
| Temperaturni opseg (Minimalno) | -10 °C          |
| Opseg temperature (maksimalni) | 90 °C           |
| Sveukupna visina               | 120 mm          |
| Ukupna širina                  | 128 mm          |
| Ukupna težina                  | 6.97 kg         |

## KUCISTE

|                 |        |
|-----------------|--------|
| ofset           | 30 mm  |
| okretni radijus | 90 mm  |
| Otpor okretanju | 180 mm |
| Prečnik kupole  | 112 mm |

## TOCAK

|               |                     |
|---------------|---------------------|
| Nošenje       | Nemašinsko glavcina |
| Prečnik       | 75 mm               |
| Širina omotac | 30 mm               |
| Širina tela   | 30 mm               |

## PRILAGOĐAVANJE

|                                  |        |
|----------------------------------|--------|
| Dužina ploče                     | 112 mm |
| Širina ploče                     | 112 mm |
| Dužina otvora ploče (maksimalna) | 92 mm  |
| Širina otvora ploče (maksimalna) | 92 mm  |
| Prečnik otvora ploče             | 9 mm   |

# FOOTMASTER

FOOT MASTER GASD-075-ASF-HUD

EAN 4031582495201

Broj porudžbine 00800105  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

