

FOOTMASTER

FOOT MASTER GASD-075-ASF-HUD

EAN 4031582495201



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	250 kg
Električni provod	no
nerdjajuci	no
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	120 mm
Ukupna širina	128 mm
Ukupna težina	6.97 kg

KUCISTE

ofset	30 mm
okretni radijus	90 mm
Otpor okretanju	180 mm
Prečnik kupole	112 mm

TOCAK

Nošenje	Nemašinsko glavcina
Prečnik	75 mm
Širina omotac	30 mm
Širina tela	30 mm

PRILAGOĐAVANJE

Dužina ploče	112 mm
Širina ploče	112 mm
Dužina otvora ploče (maksimalna)	92 mm
Širina otvora ploče (maksimalna)	92 mm
Prečnik otvora ploče	9 mm

FOOTMASTER

FOOT MASTER GASD-075-ASF-HUD

EAN 4031582495201

Broj porudžbine 00800105
Product Drawings



BETTER MOBILITY. BETTER LIFE.

