

FOOTMASTER

FOOT MASTER GATD-100-ASF-HUD

EAN 4031582495249



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel caster
Load capacity at 1.8 mph	683.43 lb
Electric conductive	no
Stainless	no
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	5.91 in
Overall width	5.16 in
Overall weight	15.45 lb

HOUSING

Offset	1.18 in
Swivel radius	3.58 in
Swivel interference	7.17 in
Dome diameter	4.09 in

WHEEL

Bearing	Unmachined hub
Diameter	3.94 in
Tread width	1.18 in
Body width	1.18 in

FITTING

Plate length	4.41 in
Plate width	4.41 in
Plate hole length (Maximum)	3.62 in
Plate hole width (Maximum)	3.62 in
Plate hole diameter	0.35 in

FOOTMASTER

FOOT MASTER GATD-100-ASF-HUD

EAN 4031582495249

Order number 00800113

Product Drawings



BETTER MOBILITY. BETTER LIFE.

