

ZETA

4681UOP200P63 XL

EAN 4031582400601



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ○ ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Zeta |
| Housing type | Swivel castor with directional lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 800 kg |
| Load capacity at 6 km/h | 640 kg |
| Load capacity Static | 1600 kg |
| Temperature range (Minimum) | -0.5 °C |
| Overall height | 240 mm |
| Overall weight | 3.199 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|---|
| Material fork | Steel sheet, very heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Offset | 55 mm |
| Swivel interference | 230 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 137 mm |
| Plate width | 105 mm |
| Plate hole length (Maximum) | 105 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 11 mm |

ZETA

4681UOP200P63 XL

EAN 4031582400601



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

