

NOVATECH

ETP080X30-Ø12 HL28_TBE

EAN 4031582438055



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	30 mm
Axle hole diameter	12 mm
Hub length	28 mm
Hardness of tread (A)	92 Shore A
Bearing type	6201

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 3 km/h	180 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.496 kg

TECHNICAL DRAWINGS

