

# MONO

A020PJ1050L51-10 CHROME

EAN 4031582364583



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Mono                        |
| Housing type                | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph    | 66.14 lb                    |
| Load capacity Static        | 132.28 lb                   |
| Temperature range (Minimum) | -4 °F                       |
| Temperature range (Maximum) | 140 °F                      |
| Overall height              | 2.83 in                     |
| Overall weight              | 1.19 lb                     |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 1.97 in                        |
| Tread width           | 0.71 in                        |
| Hardness of tread (A) | 85 Shore A                     |

## HOUSING

|                     |                 |
|---------------------|-----------------|
| Material            | Polypropylene   |
| Fork shape          | Closed          |
| Swivel bearing      | Stem, swiveling |
| Offset              | 0.98 in         |
| Swivel radius       | 2.06 in         |
| Swivel interference | 4.11 in         |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in                    |

# MONO

A020PJI050L51-10 CHROME

EAN 4031582364583



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

