

GALEA STAINLESS

5081PJC125P30-10

EAN 4031582383324



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●●○

Ishrana ●●●●○

otpornost na rdju ●●●○

OSNOVNI ATRIBUTI

| | |
|--------------------------------|----------------------------------|
| Naziv proizvoda | Galea stainless |
| Tip | Okreni Tocak sa usmerena kocnica |
| Standard | EN12530 - Kastori uređaja |
| Nosivost na 3 km/h | 100 kg |
| nerdjajuci | ✓ |
| Statički Nosivost | 200 kg |
| Temperaturni opseg (Minimalno) | -20 °C |
| Opseg temperature (maksimalni) | 60 °C |
| Sveukupna visina | 162 mm |
| Ukupna širina | 66 mm |
| Ukupna težina | 0,561 kg |

TOCAK

| | |
|----------------------------|--------------------------------------|
| Materijal za telo | polipropilen |
| materijal omotaca | Termoplastična guma |
| Nošenje | precizini kuglicni lezaj, nerdjajuci |
| stitnici omotaca | Sa threadguard |
| Prečnik | 125 mm |
| Širina omotac | 30 mm |
| Teškoća gazećeg omotac (A) | 87 Šora A |

KUCISTE

| | |
|-----------------|---|
| Materijal | poliamid |
| oblik viljuska | Zatvoreno |
| okretni lezaj | Dve trke za loptu, Ojacano ili nerdjajuci |
| ofset | 40 mm |
| okretni radijus | 129 mm |
| Otpor okretanju | 258 mm |
| Prečnik kupole | 59 mm |

PRILAGOĐAVANJE

| | |
|---------------------|----------------|
| Tip uklapanja | otvor za vijak |
| dimenzija rupa sraf | 10 mm |

GALEA STAINLESS

5081PJC125P30-10

EAN 4031582383324



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

