PRODUCT INFORMATION

# LINEA CLINIC

## 5944UAP125R36-34XS S30 D 9002

Order number 00061631



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement Noise | ●●●●○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Linea clinic |
| Type | Swivel castor with central, total or directional lock |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 3 km/h | 150 kg |
| Load capacity at 4 km/h | 150 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 450 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 130 mm |
| Overall width | 71 mm |
| Overall weight | 0.85 kg |
| Certification | Tested and monitored by TÜV Süd |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Precision ball bearing |
| Housing Color | Grey white (RAL9002) |
| Offset | 40 mm |
| Swivel radius | 108 mm |
| Swivel interference | 216 mm |
| Dome diameter | 45.5 mm |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel Color | Grey white (RAL9002) |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 15 mm |
| Body width | 15 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm |
| Bolt length | 42 mm |

Deutscher Designer Club

IF Design Award

Interzum Award

© Copyright 2026 TENTE International GmbH


# LINEA CLINIC


5944UAP125R36-34XS S30 D 9002

Order number 00061631

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



Deutscher Designer Club

IF Design Award

Interzum Award

© Copyright 2026 TENTE International GmbH