

ALPHA STAINLESS

8478IDG100P62 tread-1023

EAN 4031582347098



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ○ ○ ○
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall Height	128 mm
Overall width	85 mm
Overall weight	0.61 kg

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Housing Color	Stainless steel

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Damping, heat resistant
Bearing	Dry bearing bush
Axle	Screwed with nut
Wheel Color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Body width	35 mm
Hardness of tread (A)	75 Shore A

FITTING

Fitting type	Small rectangular plate
Plate length	100 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

ALPHA STAINLESS

8478IDG100P62 tread-1023

EAN 4031582347098

Order number 00037682

Product Drawings



BETTER MOBILITY. BETTER LIFE.

