

# MAXTECH

UAP100X20-Ø10

EAN 4031582461701



BETTER MOBILITY. BETTER LIFE.

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall weight	0.109 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm
Axle hole diameter	10 mm
Hub length	8 mm
Hardness of tread (A)	92 Shore A

# MAXTECH

UAP100X20-Ø10

EAN 4031582461701



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

