PRODUCT INFORMATION

# STYLEA

5923UAI055L51-10 black

EAN 4031582477092

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Stylea |
| Type | Swivel castor with intermittend brake |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 57 mm |
| Overall width | 37 mm |
| Overall weight | 0.65 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Stem, swiveling |
| Swivel radius | 47 mm |
| Swivel interference | 94 mm |
| Dome diameter | 18 mm |

## WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 55 mm |
| Tread width | 11 mm |
| Hardness of tread (A) | 92 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |

interzum Interzum Award

© Copyright 2026 TENTE International GmbH


# STYLEA


5923UAI055L51-10 black

EAN 4031582477092

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



Interzum Award

© Copyright 2026 TENTE International GmbH