

# NOVATECH

ETY 100X25-Ø20 HL14

EAN 4031582318852  
Order number 00830222



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	100 mm
Tread width	25 mm
Axle hole diameter	20 mm
Hub length	14 mm
Body width	25 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	210 kg
Load capacity at 6 km/h	170 kg
Load capacity Static	420 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.48 kg

# NOVATECH

ETY 100X25-Ø20 HL14

EAN 4031582318852  
Order number 00830222



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

