

# ALPHA

3478IER160P63 TFR

EAN 4031582391060



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Load capacity Static	700 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	200 mm
Overall weight	2.15 kg

## WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Hardness of tread (A)	70 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

## FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ALPHA

3478IER160P63 TFR

EAN 4031582391060



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

