

NOVATECH

FTP 300X80-Ø30 HL92

EAN 4031582331097

Broj porudžbine 00800996



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	300 mm
Širina omotac	80 mm
dimenzija rupa osovina	30 mm
dužina glavcine	92 mm
Širina tela	80 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2400 kg
Nosivost na 6 km/h	2000 kg
Statički Nosivost	4000 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	14,86 kg

NOVATECH

FTP 300X80-Ø30 HL92

EAN 4031582331097
Broj porudžbine 00800996



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

