

# PURETECH AIR

DPP400X100-Ø25 HL74 2PR

EAN 4031582317831



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                              |
|-----------------------|------------------------------|
| Body material         | Sheet Steel                  |
| Tread material        | Pneumatic tire, line profile |
| Bearing               | Precision ball bearing       |
| Threadguards          | With threadguard             |
| Diameter              | 15.75 in                     |
| Tread width           | 3.94 in                      |
| Axle hole diameter    | 0.98 in                      |
| Hub length            | 2.91 in                      |
| Hardness of tread (A) | 55 Shore A                   |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                          |              |
|--------------------------|--------------|
| Product name             | Puretech air |
| Housing type             | Wheel        |
| Load capacity at 1.8 mph | 440.92 lb    |
| Load capacity Static     | 881.85 lb    |
| Overall weight           | 5.4 lb       |

# PURETECH AIR

DPP400X100-Ø25 HL74 2PR

EAN 4031582317831



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

