

FOOTMASTER

FOOT MASTER GD- 60-F-NYN

EAN 4031582413205



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	280 kg
Electric Conductive	No
Stainless	No
Load capacity Static	280 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	82 mm
Overall width	70 mm
Overall weight	0.7 kg

HOUSING

Housing Color	White
Offset	36 mm
Swivel radius	61 mm
Swivel interference	122 mm
Dome diameter	70 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	50 mm
Tread width	25 mm
Body width	25 mm

FITTING

Plate length	73 mm
Plate width	73 mm
Plate hole length (Maximum)	58 mm
Plate hole width (Maximum)	58 mm
Plate hole diameter	7 mm

FOOTMASTER

FOOT MASTER GD- 60-F-NYN

EAN 4031582413205

Order number 00062068
Product Drawings



BETTER MOBILITY. BETTER LIFE.

