

## LINEA LIGHT

5920UAI065L51-10 RAL9002

EAN 4031582419252



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ● ○

## OSNOVNI ATRIBUTI

Naziv proizvoda Linea light

Tip kućišta Okretanje Tocak

Standard EN12528 - točkovi za nameštaj

Nosivost na 3 km/h 60 kg

Statički Nosivost 120 kg

Temperaturni opseg (Minimalno) -10 °C

Opseg temperature (maksimalni) 40 °C

Sveukupna visina 68 mm

Ukupna širina 46 mm

Ukupna težina 0,103 kg

## TOCAK

|                            |                            |
|----------------------------|----------------------------|
| Materijal za telo          | poliamid                   |
| materijal omotaca          | Poliuretan, liveno         |
| Nošenje                    | klizni lezaj sa caura cevi |
| stitnici omotaca           | Bez stražara               |
| Prečnik                    | 65 mm                      |
| Širina omotac              | 13,9 mm                    |
| Teškoća gazećeg omotac (A) | 87 Šora A                  |

## KUCISTE

|                 |                      |
|-----------------|----------------------|
| Materijal       | poliamid             |
| oblik viljuska  | kuciste za dva Tocak |
| okretni lezaj   | stablo , okretanje   |
| okretni radijus | 56 mm                |
| Otpor okretanju | 112 mm               |
| Prečnik kupole  | 23 mm                |

## PRILAGOĐAVANJE

|                     |                                    |
|---------------------|------------------------------------|
| Tip uklapanja       | zatvorena rupa za postavljanje B10 |
| dimenzija rupa sraf | 10 mm                              |

Deutscher  
dizajner  
ClubInterzum  
nagradaIF nagrada za  
Dizajn

# LINEA LIGHT

5920UAI065L51-10 RAL9002

EAN 4031582419252



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI



Deutscher  
dizajner  
Club



Interzum  
nagrada



IF nagrada za  
Dizajn