

# COMPACTA

1430PJI032P60-38X32 TES

EAN 4031582456523



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Compacta                  |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 70 kg                     |
| Load capacity Static        | 140 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 42.5 mm                   |
| Overall width               | 26 mm                     |
| Overall weight              | 0.071 kg                  |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Wheel color           | Silver grey (RAL7001)          |
| Threadguards          | Without threadguard            |
| Diameter              | 32 mm                          |
| Tread width           | 14 mm                          |
| Body width            | 15 mm                          |
| Hardness of tread (A) | 87 Shore A                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Steel sheet, light |
| Fork shape          | Broad              |
| Swivel bearing      | One ball race      |
| Colour              | Blue passivated    |
| Offset              | 11 mm              |
| Swivel radius       | 27 mm              |
| Swivel interference | 54 mm              |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 38 mm             |
| Plate width                 | 32 mm             |
| Plate hole length (Maximum) | 24 mm             |
| Plate hole width (Maximum)  | 30 mm             |
| Plate hole diameter         | 4.2 mm            |

PRODUCT INFORMATION

# COMPACTA

1430PJI032P60-38X32 TES

EAN 4031582456523



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

