

# PURETECH

PVR 125X37-Ø12 HL44

EAN 4031582321265  
Order number 00030955



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.46 in
Axle hole diameter	0.47 in
Hub length	1.73 in
Body width	1.46 in
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.03 lb

PRODUCT INFORMATION

# PURETECH

PVR 125X37-Ø12 HL44

EAN 4031582321265  
Order number 00030955



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

