

# STYLEA

5920UOI075P41-38X38/10 ALU SET

EAN 4031582440546  
Order number 00772948



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Stylea                      |
| Housing type                | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 50 kg                       |
| Load capacity Static        | 100 kg                      |
| Temperature range (Minimum) | -10 °C                      |
| Temperature range (Maximum) | 40 °C                       |
| Overall height              | 87 mm                       |
| Overall width               | 53 mm                       |
| Overall weight              | 0.122 kg                    |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 75 mm                          |
| Tread width           | 8 mm                           |
| Hardness of tread (D) | 75 Shore D                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Swivel radius       | 62 mm              |
| Swivel interference | 124 mm             |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 38 mm        |
| Plate width                 | 38 mm        |
| Plate hole length (Maximum) | 27 mm        |
| Plate hole width (Maximum)  | 27 mm        |
| Plate hole diameter         | 5 mm         |