

AGILA

2478YGO075P60-67x60

EAN 4031582342000



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Agila
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	100 mm
Overall width	43 mm
Overall weight	0.16 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	43 mm

WHEEL

Body material	Polypropylene, electric conductive
Tread Material Mix	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Wheel Color	Silver grey (similar RAL7001)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	67 mm
Plate width	60 mm
Plate hole length (Minimum)	40 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	40 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

AGILA

2478YGO075P60-67x60

EAN 4031582342000

Order number 00029054
Product Drawings



BETTER MOBILITY. BETTER LIFE.

