

NOVATECH

ITP 100x40-Ø12 HL45 incl. A-set

EAN 4031582070293



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle Hole Diameter	12 mm
Hub Length	45 mm
Body width	40 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.5 kg

NOVATECH

ITP 100x40-Ø12 HL45 incl. A-set

EAN 4031582070293

Order number 00830827
Product Drawings



BETTER MOBILITY. BETTER LIFE.

