PRODUCT INFORMATION

PURETECH

FVP300x85-25

EAN 4031582429732



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Cast iron
Tread Material Mix	Solid rubber, black
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	300 mm
Tread width	85 mm
Axle Hole Diameter	25 mm
Hub Length	92 mm
Hardness of tread (A)	67 Shore A

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●○○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1920 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	14.44 kg

© Copyright 2026 TENTE International GmbH


PURETECH

FVP300x85-25

EAN 4031582429732

BETTER MOBILITY. BETTER LIFE.

Product Drawings




© Copyright 2026 TENTE International GmbH

PURETECH

FVP300x85-25

EAN 4031582499732



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH