

PLATE

P10-40x21 / 8

EAN 4031582338119



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ●●●○○

CORE ATTRIBUTES

Product name	Mounting plate
Type	Accessory
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Overall height	0.31 in
Overall weight	0.06 lb

FITTING

Fitting type	Stem with U-shaped plate
Plate length	1.57 in
Plate width	0.83 in
Plate hole length (Maximum)	1.26 in
Plate hole width (Maximum)	1.26 in
Plate hole diameter	0.16 in