

KAPPA LOAD

9658FTP300P64

EAN 4031582316346
Order number 00801481



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2400 kg
Load capacity at 6 km/h	2000 kg
Load capacity Static	4800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	355 mm
Overall weight	17.229 kg

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	300 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced

FITTING

Fitting type	Rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	140 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	15 mm

KAPPA LOAD

9658FTP300P64

EAN 4031582316346
Order number 00801481



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

