

ELASTECH

IEP 300x55-Ø25 HL60

EAN 4031582319774



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Crni mlaz (sličan RAL9005)
štitnici omotaca	Bez stražara
Prečnik	300 mm
Širina omotac	55 mm
dimenzija rupa osovina	25 mm
dužina glavčine	60 mm
Širina tela	55 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	480 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	3.87 kg

ELASTECH


IEP 300x55-Ø25 HL60

EAN 4031582319774

Broj porudžbine 00837180
Product Drawings



BETTER MOBILITY. BETTER LIFE.




ELASTECH

IEP 300x55-Ø25 H1.60

EAN 4031582319774

Broj porudžbine 00807180



BETTER MOBILITY. BETTER LIFE.