PRODUCT INFORMATION

NOVATECH

RK.ETP080x62-Ø47x18

EAN 4031582369526



Image may differ from the original product

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	80 mm
Tread width	62 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	18 mm

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	600 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

© Copyright 2026 TENTE International GmbH

NOVATECH

RK.ETP080x62-Ø47x18

EAN 4031582369526

Order number 00832666

Product Drawings





