

STYLEA

5923UOI075B10-11X20/10D20 9011/9011

EAN 4031582311075



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel caster with intermittent brake
Load capacity at 1.8 mph	110.23 lb
Electric conductive	no
Stainless	no
Load capacity Static	220.46 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.03 in
Overall width	2.13 in
Overall weight	0.34 lb

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	1.18 in
Swivel radius	2.44 in
Swivel interference	4.88 in
Dome diameter	0.79 in

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.31 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.31 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	0.79 in

STYLEA

5923UOI075B10-11X20/10D20 9011/9011

EAN 4031582311075

Order number 00071010

Product Drawings



BETTER MOBILITY. BETTER LIFE.

