

BASETECH

POO080X34-Ø12 RAL9011

EAN 4031582320732

Broj porudžbine 00002759



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
štitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	34 mm
dimenzija rupa osovina	12,1 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (D)	65 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	125 kg
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,064 kg

BASETECH

POO080X34-Ø12 RAL9011

EAN 4031582320732

Broj porudžbine 00002759



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

