

ZETA

4688UOO200P63 WH-w46

EAN 4031582308341



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ●   |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Zeta                          |
| Type                        | Fixed caster                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 1322.77 lb                    |
| Load capacity at 3.7 mph    | 1058.22 lb                    |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 2645.54 lb                    |
| Temperature range (Minimum) | -22 °F                        |
| Temperature range (Maximum) | 176 °F                        |
| Overall height              | 9.45 in                       |
| Overall width               | 4.61 in                       |
| Overall weight              | 3.99 lb                       |

HOUSING

|                  |                         |
|------------------|-------------------------|
| Housing Material | Steel sheet, very heavy |
| Fork shape       | Broad, reinforced       |
| Housing Color    | Blue passivated         |

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Identical with wheel body |
| Bearing               | Plain bearing             |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Threadguards          | Without threadguard       |
| Diameter              | 7.87 in                   |
| Tread width           | 1.81 in                   |
| Body width            | 1.81 in                   |
| Hardness of tread (D) | 75 Shore D                |

FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.39 in           |
| Plate width                 | 4.61 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# ZETA

4688UOO200P63 WH-w46

EAN 4031582308341

Order number 00830083

Product Drawings



BETTER MOBILITY. BETTER LIFE.

