

# MAXTECH

UAD080X32-Ø12 HL44,4 BLUE

EAN 4031582496697  
Order number 00304286KK



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Diameter	80 mm
Tread width	32 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.165 kg

# MAXTECH

UAD080X32-Ø12 HL44,4 BLUE

EAN 4031582496697  
Order number 00304286KK



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

