

# PURETECH

PIR125X37-Ø15

EAN 4031582320367



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Axle hole diameter	15 mm
Hub length	58 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.488 kg

# PURETECH

PIR125X37-Ø15

EAN 4031582320367



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

